


# RTN

## Elastomerlager VEN / Elastomer mount VEN 150 t - 470 t



technische Änderungen vorbehalten  
technical changes reserved

Type	ØA	ØB	D	E	F	H	h	K	M	N	T	ØU	V	W±0.5	X
RTN/150T/VEN	100	400	10	180	140	320	81	130	M16	8	50	26	8	460	510
RTN/220T/VEN	135	450	12	260	200	373	81	180	M20	8	50	26	8	510	560
RTN/330T/VEN	135	550	12	260	200	428	96	180	M24	10	60	32	10	620	680
RTN/470T/VEN	160	650	12	320	240	520	115	220	M24	13	60	32	10	720	780

(1) = max. zul. Bewegungsspiel  
admissible play

(2) = Erdungsanschluss  
Ground connection

Abmessungen in mm / Dimensions (in mm; 1 mm = 0.03937 inches)

Änderungen vorbehalten.  
Alle Angaben beschreiben unsere Produkte in  
allgemeiner Form. Sie stellen keine  
Beschaffungs- oder Haltbarkeitsgarantie dar.

*Subject to modifications.  
All product descriptions are for general information  
only. They are not to be understood as a  
guarantee of quality or durability.*

**Hottinger Baldwin Messtechnik GmbH**  
Im Tiefen See 45 · 64293 Darmstadt · Germany  
Tel. +49 6151 803-0 · Fax +49 6151 803-9100  
Email: [info@hbm.com](mailto:info@hbm.com) · [www.hbm.com](http://www.hbm.com)

**measure and predict with confidence**

