



# **DT85**

External display and control unit for MP85(A) and MP85(A)DP process controller


## **Special features**

- Monitoring of fitting, press-fit and testing process in manufacturing monitoring and automation
- Graphical display of all measured values and press-fit curves with OK / NOK results and statistics function
- Parameterization and control of up to 10 MP85(A)DP amplifiers via CAN interface
- Can be connected during operation (hot plugging)
- Without fan, maintenance-free, small mounting depth






#### Graphical display



### Configuration windows



```
General Setting MP85

CAA+10 : 113
Device name : Ay Projekt
Device typ : AP850P

Program version: 1.06
Bardwareversion: 1.04/a

Serial number : 081/2010/
Date / time : 04.04.2005/14:0/:26

Bardware synchronization: Baster

MEASUR

BACK HEXT
```




## **Specifications**

DT85		
Display		Backlit LCD display, monochrome background illumination with auto contrast function
Resolution	Pixel	320 x 240 (5.7 Zoll)
Active screen	mm	120 x 90
Face plate		plexiglas
Operation		6 function keys with tactile touch and encoder wheel
Password		Several input levels can be protected by password
Dialog		Menu language switchable German or English
Supply voltage	$V_{DC}$	18 30
Power consumption, max.	W	5
Electrical connection		2 x CAN-Bus (electrical separated), 4-pin COMBICON connector 1 x supply / 3-pin COMBICON connector 1 x RS232 for maintenance
Nominal (rated) temperature range	Co	0 +50
Storage (rated) temperature range	Co	-20 +70
Humidity rel.	%	20 80 (not condensating)
Vibration (5-65 Hz), max. 3 times in each direction	m/s <sup>2</sup>	50
Shock (11 ms), max. 3 times in each direction	m/s <sup>2</sup>	200
Dimensions	mm	216 x 158 x 45 (w x h x d)
Mounting		8 fixing bolts M3
Cutout in the panel frame	mm	185 x 130 (w x h)
Degree of protection		IP52 front side, IP20 back side
Weight , approx.	g	800

The display and control unit (display terminal) provides a comfortable graphical overview and handling of the various funchions of the MP85(A)DP measuring amplifiers without any additional hard/software. The DT85 features a graphical display with a bright background illumination.

The display and control unit is operated using six function keys with tactile touch and a rotary switch with a key function for easy menu navigation



© Hottinger Baldwin Messtechnik GmbH.
Modifications reserved. All details describe our products in general form only. They are not to be understood as a guarantee of quality or durability and do not constitute any liability whatsoever.

#### Hottinger Baldwin Messtechnik GmbH

Im Tiefen See 45 · 64293 Darmstadt · Germany Tel. +49 6151 803-0 · Fax: +49 6151 803-9100 E-mail: info@hbm.com · www.hbm.com

