



OIML Member State
The Netherlands

OIML Certificate N° R60/2000-NL1-05.04
Project number 412528
Page 1 of 2

OIML CERTIFICATE OF CONFORMITY

Issuing Authority

Name: NMI Certin B.V.
Address: Hugo de Grootplein 1, Dordrecht
Person responsible: Ing. C. Oosterman

Applicant

Name: Hottinger Baldwin Messtechnik GmbH
Address: Im Tiefen See 45
D-64293 Darmstadt
Germany

Manufacturer of the certified type

Name: Hottinger Baldwin Messtechnik GmbH
Address: Im Tiefen See 45
D-64293 Darmstadt
Germany

Identification of the certified type

Type : PW20i
Fraction : $P_i = 1$
Temperature range -10 °C / +40 °C

Maximum capacity (E_{\max})	5 kg up to and including 50 kg
Accuracy Class	C
Maximum number of load cell intervals (n)	3000
Ratio of minimum LC Verification interval $Y = E_{\max} / V_{\min}$	10000



Nederlands Meetinstituut

OIML Member State
The Netherlands

OIML Certificate N° R60/2000-NL1-05.04

Project number 412528

Page 2 of 2

This Certificate attests the conformity of the above identified type (represented by the sample or samples identified in the associated Test Report, the test certificate and the description with number TC6740 and the appertaining documentation folder), with the requirements of the following Recommendation of the International Organization of Legal Metrology (OIML):

R60
Edition 2000 (E)
for accuracy class C

This Certificate relates only to the metrological and technical characteristics of the type of the instrument covered by the relevant OIML International Recommendation identified above.

This Certificate does not bestow any form of legal international approval.

The conformity was established by the results of tests and examinations provided in the associated Test Reports:

N° R60/2000-NL1-05.04A that includes 53 pages;

N° R60/2000-NL1-05.04B that includes 37 pages.

The Issuing Authority
Ing. C. Oosterman
Manager Product Certification

25 April 2005

The OIML Member
Dr. ir. C.J. van Mullem

25 April 2005

*
* *

Important note: Apart from the mention of the Certificate's reference number and the name of the OIML Member State in which the Certificate is issued, partial quotation of the Certificate and of the associated Test Report is not permitted, although either may be reproduced in full.