

# PW2D... Single point load cells


with  
 **IO-Link**  
option

## SPECIAL FEATURES

- Max. capacities: 7.2 kg ... 72 kg
- Aluminum
- High ratio of minimum verification interval Y
- Optimized for dynamic weighing applications
- Shielded connection cable
- Different cable lengths and other options available
- Available as LCMC measurement chain with smart option (IO-Link), with digital option (CANopen or RS-485), with analog option (4 ... 20 mA or 0 ... 10 V)



## DIMENSIONS



## SPECIFICATIONS

Type			PW2D...				
Accuracy class according to OIML R60 <sup>1)</sup>			C3 Multi Range (MR)				
Maximum number of load cell intervals	$n_{LC}$		3000				
Maximum capacity	$E_{max}$	kg	7.2	12	18	36	72
Minimum LC verification interval	$v_{min}$	g	0.5	1	2	5	10
Temperature effect on zero balance	$TK_0$	% of $C_n/10$ K	±0.0097	±0.0116	±0.0155	±0.0194	±0.0194
Ratio of minimum verification interval	Y		14,400	12,000	9,000	7,200	
Accuracy class according to NTEP <sup>2)</sup>			III S				
Maximum number of load cell intervals	$n_{LC}$		3000				
Maximum capacity	$E_{max}$	kg	7.2	12	18	36	72
Minimum LC verification interval	$v_{min}$	g	0.5	1	2	5	10
Ratio of minimum verification interval	Y		14,400	12,000	9,000	7,200	
General specifications							
Max. platform size		mm	380 x 380				
Sensitivity	$C_n$	mV/V	2.0 ±0.2 (Option 6: A = 2mV/V ±0.1%)				
Zero signal		mV/V	0 ±0.1				
Temperature effect on sensitivity <sup>3)</sup> in the temperature range +20 ... +40 °C [+68 ... +104 °F] -10 ... +20 °C [+14 ... +68 °F]	$TK_C$	% of $C_n/10$ K	±0.0175 ±0.0117				
Relative reversibility error <sup>3)</sup>	$d_{hy}$	% of $C_n$	±0.0166				
Linearity deviation <sup>3)</sup>	$d_{lin}$		±0.0166				
Minimum dead load output return	DR		±0.0166				
Off-center load error <sup>4)</sup>			±0.0233				
Input resistance	$R_{LC}$	Ω	300...500				
Output resistance	$R_0$		300...500 (Option 6: A = 410 Ω ±0.2 Ω)				
Reference excitation voltage	$U_{ref}$	V	5				
Nominal range of excitation voltage	$B_u$		1 ... 12				
Maximum excitation voltage			15				
Isolation resistance at 100 V <sub>DC</sub>	$R_{is}$	GΩ	> 2				
Nominal (rated) range of ambient temperature	$B_T$	°C [°F]	-10 ... +40 [+14 ... +104]				
Operating temperature range	$B_{tu}$		-10 ... +50 [+14 ... +122]				
Storage temperature range	$B_{tl}$		-25 ... +70 [-13 ... +158]				
Limit load at max. 160 mm eccentricity	$E_L$	% of $E_{max}$	150				
Lateral load limit, static	$E_{lq}$		300				
Service load at max. 100 mm eccentricity	$E_U$		150				
Breaking load at max. 20 mm eccentricity	$E_d$		300				
Relative permissible oscillation stress at max. 20 mm eccentricity	$F_{srel}$		70				
Nominal (rated) displacement at $E_{max}$ , approx.	$s_{nom}$		mm	0.15	0.13	0.12	0.12
Natural frequency, approx.		Hz	340	460	600	840	1140
Weight, approx.	m	kg	0.25				
Degree of protection <sup>5)</sup>			IP67				
Material Measuring body Application protection Cable sheath			Aluminum Silicone caoutchouc PVC				

1) With  $P_{LC} = 0.7$

2) Only with 4 wire cable

3) The values for linearity deviation ( $d_{lin}$ ), relative reversibility error ( $d_{hy}$ ) and temperature effect on sensitivity ( $TK_C$ ) are recommended values. The sum of these values remain within the cumulated error limit according to OIML R60.


4) According to OIML R76

5) According to EN 60 529 (IEC 529)

## WIRING CODE

### Connection with 4 wire cable (cable length: 0.35 m)

Detailed description of the Pancon plug (CE100F26-4), 4-pole



Shield (yellow) = Shield connected to load cell body

Plug-in contact 1 (blue) = Excitation (+)

Plug-in contact 2 (white) = Signal (+)


Plug-in contact 3 (red) = Signal (-)

Plug-in contact 4 (black) = Excitation (-)

blue marking

### Connection with 6 wire cable, 6 x 0.14 mm<sup>2</sup>/AWG 26 (cable length, selectable: 0.35 m; 1.5 m; 3 m; 6 m)

Schematic diagram of a TE connector (TE 3-640442-6), 6-pole



Plug-in contact 4 (blue [BU]) = excitation voltage (+)

Plug-in contact 5 (green [GN]) = sense line (+)

Plug-in contact 1 (white [WH]) = measurement signal (+)

Plug-in contact 3 (black [BK]) = excitation voltage (-)

Plug-in contact 6 (gray [GY]) = sense line (-)

Plug-in contact 2 (red [RD]) = measurement signal (-)

Shield (yellow [YI]) = Cable shield


## MOUNTING AND LOAD APPLICATION

The load cells are fixed at the mounting bores. For the recommended screws and tightening torques refer to the table below:

Max. capacity	Thread	Min. property class	Tightening torque <sup>1)</sup>
7.2...36 kg	M6	8.8	6 N·m
72 kg	M6	10.9	10 N·m

<sup>1)</sup> Recommended value for the stated property class. For screw dimensioning please refer to the appropriate information given by the screw manufacturers.

Load must not be applied to the side where the cable connection is located, as this would cause a force shunt.



## ORDERING DESIGNATIONS

### PW2D... / K-PW2D-...

Optimized for dynamic applications

PW2D... (Aluminum)

<b>Type</b>	PW2D
<b>Accuracy</b>	OIML R60 C3MR / NTEP III S 3000
<b>Note</b>	Cable length 0.35 m (4 wire)
<b>Capacity</b>	<b>Order no.</b>
7,2 kg	1-PW2DC3/7.2KG-1
12 kg	1-PW2DC3/12KG-1
18 kg	1-PW2DC3/18KG-1
36 kg	1-PW2DC3/36KG-1
72 kg	1-PW2DC3/72KG-1

### K-PW2D... (Aluminum), optional versions

<b>K-PW2D</b>		
<b>1</b>	<b>Code</b>	<b>Option 1: Mechanical version</b>
	<b>N</b>	-
<b>2</b>	<b>Code</b>	<b>Option 2: Accuracy</b>
	<b>C3MR</b>	C3MR (OIML) (Multi Range)
<b>3</b>	<b>Code</b>	<b>Option 3: Capacity</b>
	<b>7.2</b>	7.2 kg
	<b>12</b>	12 kg
	<b>18</b>	18 kg
	<b>36</b>	36 kg
<b>4</b>	<b>Code</b>	<b>Option 4: NN</b>
	<b>N</b>	-
<b>5</b>	<b>Code</b>	<b>Option 5: Cable length</b>
	<b>4_0.35</b>	0.35 m (4 wire) (Standard)
	<b>6_0.35</b>	0.35 m (6 wire)
	<b>6_1.5</b>	1.5 m (6 wire)
	<b>6_3</b>	3 m (6 wire)
	<b>6_6</b>	6 m (6 wirer)
<b>6</b>	<b>Code</b>	<b>Option 6: Miscellaneous</b>
	<b>N</b>	Without
	<b>A</b>	2mV/V ±0.1% / 410 Ohm ±0.2 Ohm (aligned output, suitable for connection in parallel)

K-PW2D - 

<b>N</b>
----------

 - 

<b>C</b>	<b>3</b>	<b>M</b>	<b>R</b>
----------	----------	----------	----------

 - 

--	--	--

 - 

<b>N</b>
----------

 - 

--	--	--	--	--	--


 - 

--

1                      2                      3                      4                      5                      6

## LCMC - LOAD CELL MEASURING CHAIN

A wide range of famous load cells combined with a choice of excellent measuring electronics makes your tailored Load Cell Measuring Chain.



### K-LCMC-PW2D ordering options

K-LCMC		
1	Code	Option 1: Load cell type
	PW2D	PW2D
2	Code	Option 2: Accuracy class
	MR	C3 MR (OIML)
3	Code	Option 3: Nominal load
	7K20	7.2 kg
	12K0	12 kg
	18K0	18 kg
	36K0	36 kg
4	Code	Option 4: Cable length
	0M3	0.3 m
	0M5	0.5 m
	1M0	1.0 m
	3M0	3.0 m
5	Code	Option 5: Measurement electronics
	105C	CAN (200 S/s)
	105R	RS485 (200 S/s) 2-wire
	112C	CAN (1,200 S/s)
	112R	RS485 (1,200 S/s) 4-wire
	RM42	Analog 4 ... 20 mA
	RM43	Analog 0 .. 10 V
RMIO	IO-link	
6	Code	Option 6: Connector
	M12A8	M12 A-coded, male, 8-pin
	M12A4	M12 A-coded, male, 4-pin
7	Code	Option 7: Firmware version
	N	NA
	01	WTIO 1.03.00

K-LCMC - 

P	W	2	D
---	---	---	---

 - 

M	R
---	---

 - 

--	--	--	--

 - 

--	--	--	--

 - 

--	--	--	--

 - 

--	--	--	--	--	--

 - 

--	--

1                      2                      3                      4                      5                      6                      7

**Hottinger Brüel & Kjaer GmbH**

Im Tiefen See 45 · 64293 Darmstadt · Germany  
Tel. +49 6151 803-0 · Fax +49 6151 803-9100  
www.hbkworld.com · info@hbworld.com

Subject to modifications. All product descriptions are for general information only. They are not to be understood as a guarantee of quality or durability.