




## Displacement transducer

## **Special features**

- Short overall length
- Shaft diameter 8 mm
- Protection class IP67
- Good price/performance ratio

Dimensions (in mm; 1 mm= 0.03937 inches)



Туре	Α	В	С	D	E	F	G
WI/2mm-T	66	0.5	2	5	43	~12	29
WI/5mm-T	79	0.5	5	2.5	56	~12	42
WI/10mm-T	95	0.5	10	1.5	65	~16	52



## **Specifications**

Transducer type		WI/2mm-T	WI/5mm-T	WI/10mm-T		
Nominal (rated) displacement (nominal (rated) measuring span)	mm	2	5	10		
Nominal (rated) output span (between starting point and end point when output is not under load)	mV/V	80	80	80		
Nominal (rated) signal at starting point	mV/V		-40	•		
Nominal (rated) signal at end point	mV/V	40				
Nominal (rated) output span tolerance	%	±1				
Zero signal		The output signal is zero when the plunger or the probe is located in mid measuring range				
Zero signal setting tolerance	mV/V	V ±4				
Linearity deviation (max. deviation between starting point and end point (including hysteresis)						
Nominal (rated) temperature range	°C	10 60				
Operating temperature range	°C	-20 +80				
Temperature effect in the nominal (rated) temperature range						
on the zero signal, related to the nominal output span per 10 K	%	±0.1	±0.1	± 0.1		
on the nominal (rated) output span related to the actual value per 10 K	%	±0.2	±0.2	± 0.2		
Weight						
of measuring element without connection cables	g	12	15	20		
of moving parts	g	4.25	4.8	5.5		
Amount of input impedance	Ω	27	42	45		
Nominal (rated) excitation voltage (effective)	V <sub>eff</sub>	2.5				
Operating range of excitation voltage	V <sub>eff</sub>	0.5 10				
Carrier frequency	Hz	4800 ±8%				
Degree of protection as per EN 60529 for transducer duct and core channel	-	IP67				
Surface materials	-		rustproof			
Load capacity with vibration sinusoidal DIN40046/8 IEC Part 2-6 (type-tested)						
Frequency range	Hz	5 to 65				
Vibration acceleration	m/s <sup>2</sup>	150				
Duration (per direction)	h		0.5			
Load capacity with mechanical shock Sheet 26 (type-tested)						
Number of impacts (per direction)	-	1000				
Impact acceleration	m/s <sup>2</sup>	650				
Impact duration	ms	Ŭ				
Impact form	- N1/	0.05	Half sine wave	0.4		
Spring constant	N/mm	0.05	0.05	0.1		
Spring force at starting point	N N	0.0	0.8	4.0		
Spring force at end point	N	0.9	1.05	1.8		
Max. permissible acceleration of probe tip and plunger, approx.	m/s <sup>2</sup>	180	160	140		
Cut-off frequency of probe tip	U <b>-</b>	69	64	60		
at ±1 mm stroke, approx.	Hz Hz	68 68	64 40	60 27		
at maximum stroke, approx.		00	l			
Cable length, approx.	m	3 PU black				

## **Accessory**

Assembly set, mounting block 8 mm, tool Order no.: 1-WZB8

Subject to modifications.
All product descriptions are for general information only. They are not to be understood as a guarantee of quality or durability.

Hottinger Baldwin Messtechnik GmbH Im Tiefen See 45 · 64293 Darmstadt · Germany Tel. +49 6151 803-0 · Fax +49 6151 803-9100 Email: info@hbm.com · www.hbm.com

