

Issued by NMI Certin B.V.

In accordance with WELMEC 8.8 2017, WELMEC 2.4 Issue 2, OIML R 60 (2000), EN 45501:2015.

Producer Hottinger Baldwin Messtechnik GmbH
Im Tiefen See 45
D-64293 Darmstadt
Germany

Measuring instrument A **single point load cell**, with strain gauges, tested as a part of a weighing instrument.

Brand : HBM
Designation : PW6C...

Further properties are described in the annexes:

- Description TC11683 revision 0;
- Documentation folder TC11683-1.

An overview of performed tests is given in the annex:

- Description TC11683 revision 0.

Issuing Authority

NMI Certin B.V.
23 July 2019


C. Oosterman
Head Certification Board

1 General information about the load cell

All properties of the load cell, whether mentioned or not, shall not be in conflict with the standards mentioned in this certificate.

This certificate is the positive result of the applied voluntary, modular approach, for a component of a measuring instrument, as described in WELMEC 8.8. The complete measuring system must be covered by an EC type-approval certificate, an EC-type examination certificate or an EU-type examination certificate.

1.1 Essential parts

Number	Pages	Description	Remark
11683/0-01	4	PW6C... datasheet	Mechanical
11683/0-02	1	Wiring diagram	Electrical

Cable:

- If the load cell is provided with a 4-wire system:
 - The cable length is mentioned in the accompanying load cell document / on the label;
 - The cable length has to be 0,5 meters or 0,35 meters;
 - The cable length shall not be modified.
- If the load cell is provided with a 6-wire system (=“Remote-sensing”):
 - The cable length is not limited.

The cable is shielded; the shield is connected to the load cell.

1.2 Essential characteristics

Maximum capacity (E_{max})	1,5 kg up to 3 kg	3 kg up to and including 40 kg
Minimum dead load	0 kg	
Accuracy Class	C	
Rated Output	2,2 mV/V	
Maximum number of load cell intervals (n) ⁽¹⁾	5000	6000
Ratio of minimum LC Verification interval ⁽¹⁾ $Y = E_{max} / V_{min}$	20000	25000
Ratio of minimum dead load output return ⁽¹⁾ $Z = E_{max} / (2 * DR)$	7500	
Input impedance	400 Ω \pm 100 Ω	
Temperature range	-10 $^{\circ}$ C / + 40 $^{\circ}$ C	
Fraction p_{LC}	0,7	
Humidity Class	CH	

Safe overload	150 % of E_{max}
Output impedance	$400 \Omega \pm 100 \Omega$
Recommended excitation	5 V AC / DC
Excitation maximum	15 V AC / DC
Transducer material	Aluminium
Atmospheric protection	Silicone rubber

Remark:

1. The characteristics for n_{max} , Y and Z can be reduced separately.

1.3 Essential shapes

Number	Pages	Description	Remark
11683/0-01	4	PW6C... datasheet	Mechanical

The descriptive markings plate is secured against removal by sealing or will be destroyed when removed and contains at least the information and markings as described in OIML R 60 (2000) and:

- This certificate number TC11683 (in the countries where it is mandatory);
- Producers name or mark.

2 Seals

The connecting cable of the load cell or the junction box is provided with possibility to seal.

3 Conditions for conformity assessment

Each load cell produced is provided with an accompanying document with information about its characteristics.

The compatibility of load cells and indicator is established by the manufacturer by means of the compatibility of modules form, contained in WELMEC 2, 2015 clause 10, at the time of putting into use.

Other parties may use this certificate without the written permission of the producer (WELMEC 8.8).

4 Reports

An overview of performed tests is given in the reports:

- No. NMI-2372291-01 dated 18 July 2019 that includes 46 pages;
- No. NMI-2372291-02 dated 18 July 2019 that includes 51 pages;
- No. NMI-2372291-03 dated 18 July 2019 that includes 46 pages;

A report can be a test report, an evaluation report, a type evaluation report and/or a pattern evaluation report.