

DATA SHEET

WE2107M



Weighing indicator (NAWI) in stainless steel housing

SPECIAL FEATURES

- OIML test report to 6000 d
- Use as 1, 2 or 3-range scale
- Four limit value switches with hysteresis
- RS 485 interface
- Two digital control inputs
- Four digital outputs (limit value switches or filling/batching control)
- Degree of protection IP65



DIMENSIONS



Dimensions in mm (1 mm = 0.03937 inches)

SPECIFICATIONS

Type		WE2107M
Max. number of calibration values as per OIML R76 (Class III, IIII)	d = e	6000; Multirange
Multi-range application	d = e	2x3000; 3x2000
Input sensitivity	$\mu\text{V}/e$	≥ 0.6 ¹⁾
Measuring range	mV/V	± 2 ; max. ± 3.2
Minimum load cell resistance	Ω	58
Maximum load cell resistance	Ω	4000
Load cell supply	V_{DC}	5
Cable length between WE2107 and load cell(s)	m	max. 100 (206 m/mm ²) ¹⁾
Data rate	Meas./s	200
Filter, adjustable, FMD0 Cut-off frequency (-3 dB)	Hz	0.0625 0.125 0.25 0.5 1 2 4 8 25
Settling time	ms	16000 8000 4000 2000 1000 500 250 125 80
FMD1 Cut-off frequency (-3 dB)	Hz	2 2.5 3 4 5 6 7 8 10
Settling time	ms	566 450 380 310 240 170 160 150 140
Voltage supply without connected analog output	V_{DC}	12...30; 24 nominal
Voltage supply with connected analog output	V_{DC}	18 ... 30; 24 nominal
Power consumption (incl. lighting)	W	6
Display		LCD with backlighting
Character height	mm	20
Status display		Zero, net, standstill, unit, range
Keys		Membrane keypad (tactile feedback)
Number of digital inputs		2
Input voltage IN1/2, Low	V	0...1.0
Input voltage IN1/2, High	V	3...30
Input resistance	k Ω	10
Number of digital outputs (High side switch)		4
Max. output current/output	A	0.6
Voltage supply, outputs	V	12...30; 24 nominal
Interface (COM1)		RS 485
Baud rate, adjustable	Bd	1200 ... 38400
Interface functions (COM2)		Print, serial display (automatic output), PC connection via RS 232
Nominal (rated) temperature range	$^{\circ}\text{C}$	-10 ... +50 (-10 ... +40) ¹⁾
Operating temperature range	$^{\circ}\text{C}$	-20 ... +60
Storage temperature range	$^{\circ}\text{C}$	-40 ... +85
Weight, approx.	kg	1
Degree of protection per EN 60 529 (IEC 529)		IP65 (front only)
Interference immunity (EMC) as per EN 45 501 (3 V/m)		Additionally tested to 10 V/m
Housing material		Stainless steel (front only)

¹⁾ In accordance with OIML R76, legal for trade

Order No.: 1-WE2107M-SS-1


Accessories

Included in scope of supply:

- CD ROM with WE2107 Panel Program
- Command description for PC connection
- Documentation

To be ordered separately:

- Plug-in power supply unit (100 ... 240 V), do not use for operation with analog output, Order No.: 1-AC/DC15V/550mA



Housing: Degree of protection IP40

Dimensions in mm (1 mm = 0.03937 inches)

Hottinger Brüel & Kjaer GmbH

Im Tiefen See 45 · 64293 Darmstadt · Germany
Tel. +49 6151 803-0 · Fax +49 6151 803-9100
www.hbkworld.com · info@hbkworl.com

Subject to modifications. All product descriptions are for general information only. They are not to be understood as a guarantee of quality or durability.