

DATA SHEET






PW12C... Single point load cells




SPECIAL FEATURES

- · Maximum capacities: 50 kg ... 750 kg
- Aluminum
- · High ratio of minimum verification interval Y
- · Off-center load compensation
- · Complies with EMC directives
- Six-wire circuit
- Explosion protection and other options also available
- Available as LCMC measurement chain with smart option (IO-Link), with digital option (CANopen or RS-485), with analog option (4 ... 20 mA or 0 ... 10 V)



DIMENSIONS



SPECIFICATIONS

Туре	PW12C													
Accuracy class ¹⁾	C3 Multi Range (MR)													
Number of load cell verification intervals	n _{LC}						30	00						
Maximum capacity ²⁾	E _{max}	kg	50	75	100	150	200	250	300	500	635	750		
Minimum load cell verification interval, accuracy class C3MR	v _{min}	g	5	5	10	10	20	20	20	50	50	50		
Temperature coefficient of zero signal, accuracy class C3MR	TC ₀	% of C _n / 10 K	±0.0140	€600.0∓	±0.0140	±0.0093	±0.0140	±0.0112	€600.0∓	±0.0140	±0.0110	±0.0093		
Ratio of minimum verification interval		Υ	10,000	15,000	10,000	15,000	10,000	12,500	15,000	10,000	12,700	15,000		
Maximum platform size		mm					800 x	800						
Nominal sensitivity	C _n	mV/V			2.0 :	±0.2 (Օր	tion 6:	A = 2m	V/V ± 0	.1%)				
Zero signal		111V/V	0 ±0.1											
Temperature coefficient of sensitivity ³⁾ Temperature range: +20 +40 °C -10 +20 °C	itivity ³⁾ TC _c % of C _n / 10K ±0.0175													
Relative reversibility error ³⁾	d _{hy}						±0.0							
Non-linearity ³⁾	d _{lin}	0, 60	±0.0166											
Minimum dead load output return	DR	% of C _n	±0.0166											
Off-center load error ⁴⁾			±0.0233											
Input resistance	R _{LC}	Ω	300 500 300 500 (Option 6: A = 410 Ω ± 0.2 Ω)											
Output resistance	R ₀				300	. 500 (C	-		0 Ω ± 0).2 Ω)				
Reference excitation voltage Nominal (rated) range of the	U _{ref}	V	5 1 12											
excitation voltage			15											
Maximum excitation voltage Insulation resistance at 100 V _{DC}	B _U	GΩ	15 > 2											
Nominal (rated) range of the	R _{is}	GΩ					-10							
ambient temperature		°C												
Operating temperature range	B _{tu}	Ŭ					-10							
Storage temperature range	B _{tl}						-25							
Limit load at max. 100 mm eccentricity	EL						15							
Limit lateral loading, static	E _{lq}						30	00						
Service load at max. 100 mm eccentricity	Eu	% of					15	50						
Breaking load at max. 20 mm eccentricity	E _d	E _{max}					30	00						
Relative permissible oscillation stress at max. 20 mm eccentricity	F _{srel}		70											
Rated displacement at E _{max} , approx.	s _{nom}	mm					< 0).5						
Weight, approx.	m	kg					2.	4						


Туре	PW12C
Degree of protection ⁵⁾	IP67
Material	
Measuring body Covering agent	Aluminum Silicone rubber
Cable sheath	PVC


 $[\]frac{1}{2}$ As per OIMLR60, with P_{LC} = 0.7


CABLE ASSIGNMENT

6-wire cable connection, 6 x 0.14 mm²/AWG 26 (available cable lengths: 1.5 m; 3 m; 6 m; 12 m)

Schematic diagram of a TE connector (TE 3-640442-6), 6-pin







Plug-in contact 4 (blue [BU]) = excitation voltage (+)

Plug-in contact 5 (green [GN]) = sense line (+)

Plug-in contact 1 (white [WH]) = measurement signal (+)

Plug-in contact 3 (black [BK]) = excitation voltage (-)

Plug-in contact 6 (gray [GY]) = sense line (-)

Plug-in contact 2 (red [RD]) = measurement signal (-)

Shield (yellow [YN]) = Cable shield

²⁾ Maximum eccentric loading as per OIML R76

³⁾ If the values for non-linearity (d_{lin}), relative reversibility error (d_{hy}) and temperature coefficient of sensitivity (TC_C) are added together, they are within the cumulated error limit specified in OIML R60.

⁴⁾ Off-center load deviation per OIML R76

⁵⁾ As per EN 60 529 (IEC 529)


MOUNTING AND LOAD APPLICATION

The load cells are attached at the mounting holes, the load is applied at the other end. The recommended screws and tightening torques can be found in the table below:

Maximum capacities	Thread	Min. property class	Tightening torque ¹⁾
50500 kg	M8	10.9	35 N·m
635 kg, 750 kg	M8	12.9	42 N·m

¹⁾ Recommended value for the specified property class. Please comply with the screw manufacturer's instructions with regard to screw dimensions

Load must not be applied to the side where the cable connection is located, as this would cause a force shunt.



PRODUCT NUMBERS

PW12C... (aluminum)

Туре	PW12C
Accuracy class	C3-MR (OIML) (Multi Range)
Comments	Cable length 3 m (6-wire)

Maximum capacity [kg]	Ordering number
50	1-PW12CC3/50KG-1
75	1-PW12CC3/75KG-1
100	1-PW12CC3/100KG-1
150	1-PW12CC3/150KG-1
200	1-PW12CC3/200KG-1
250	1-PW12CC3/250KG-1
300	1-PW12CC3/300KG-1
500	1-PW12CC3/500KG-1
635	1-PW12CC3/635KG-1
750	1-PW12CC3/750KG-1

K-PW12C-... (aluminum), optional versions

K-PW12C		
4	Code	Option 1: Mechanical design
1	N	-
	Code	Option 2: Accuracy class
2	MR	C3-MR (OIML) (Multi Range)
	Code	Option 3: Nominal load
	50	50 kg
	75	75 kg
	100	100 kg
	150	150 kg
3	200	200 kg
	250	250 kg
	300	300 kg
	500	500 kg
	635	635 kg
	750	750 kg
	Code	Option 4: Explosion protection
4	N	No explosion protection
4	Al1/21	ATEX+IECEx+FM Zone 1/21, intrinsically safe; II 2G Ex ia IIC T6/T4 Gb + II 2D Ex ia IIIC T125°C Db*
	Al2/22	ATEX+IECEx Zone 2/22, not intrinsically safe; II 3G Ex ec IIC T6/T4 Gc + II 3D Ex tc IIIC T125°C Dc*
	Code	Option 5: Cable length
	1.5	1.5 m
5	3	3 m (standard)
	6	6 m
	12	12 m
	Code	Option 6: Other
6	N	Without
	Α	2 mV/V $\pm 0.1\%$ / 410 Ω \pm 0.2 Ω (adjusted output, suitable for parallel connection)

K-PW12C	- [N	-	M R] -] -					-		-		
		1		2		3			_	1			5		6	

^{*} Including EC-Type Examination Certificate/Certificate of Conformity BVS 13 ATEX X 108 X/IECEx BVS 13.0109 X


LCMC - LOAD CELL MEASURING CHAIN

A wide range of famous load cells combined with a choice of excellent measuring electronics makes your tailored Load Cell Measuring Chain.

Option 1: Load cell type Option 2: Accuracy class
Option 3: Nominal load
Option 4: Cable length

Option 5: Measurement electronics \(\)

Option 6: Connector Option 7: Firmware version



K-LCMC-PW12C ordering options

_	Code	Option 1: Load cell type
1	PW12C	PW12C
	Code	Option 2: Accuracy class
2	MR	C3 MR (OIML)
	Code	Option 3: Nominal load
	50K0	50 kg
	75K0	75 kg
	100K	100 kg
	150K	150 kg
3	200K	200 kg
	250K	250 kg
	300K	300 kg
	500K	500 kg
	635K	635 kg
	750K	750 kg
	Code	Option 4: Cable length
	0M3	0.3 m
4	0M5	0.5 m
	1M0	1.0 m
	3M0	3.0 m
	Code	Option 5: Measurement electronics
	105C	CAN (200 S/s)
	105R	RS485 (200 S/s) 2-wire
	112C	CAN (1,200 S/s)
5	112R	RS485 (1,200 S/s) 4-wire
	RM42	Analog 4 20 mA
	RM43	Analog 0 10 V
	RMIO	IO-link
	Code	Option 6: Connector
6	M12A8	M12 A-coded, male, 8-pin [only with option 5 = 105C, 105R, 112C, 112R, RM42, RM4
	M12A4	M12 A-coded, male, 4-pin [only with option 5 = RMI
	Code	Option 7: Firmware version
7	N	NA [only with option 5 = 105C, 105R, 112C, 112R, RM42, RM4
	01	WTIO 1.07 [only with option 5 = RMI

5

6

7

2

3

Hottinger Brüel & Kjaer GmbH

Im Tiefen See 45 · 64293 Darmstadt · Germany Tel. +49 6151 803-0 · Fax +49 6151 803-9100 www.hbkworld.com · info@hbkworld.com