




PACEline CMA


Charge amplifier

Special features

- Compact, robust design
- Two measuring ranges 5:1
- CMA5000/2 with two parallel sensor inputs
- TEDS sensor detection
- Measuring range externally switchable
- Signal output ±10 V
- All signal inputs/outputs electrically isolated

CMA block diagram





CMA charge amplifier





Specifications (data per VDI/VDE/DKD 2638 standards)


Charge amplifier	CMA1 to CMA2000												CMA5000/2	
Transducers that can be connected					Pie	ezoe	electric	sens	sors (passiv	re)			
Max. charge input	nC	1 2	5	20	39.5	158.	3	210.5	2	87	482	2	2000	5000
Calibrated measuring ranges 1)	% F _{nom}	,	ı	1	1	ı	ı		100; 2	20	ı	ı	l	
Time for measuring range conversion	μs								250					
Output voltage	V								±10)				
On time for secure output signal	ms								4					
Accuracy class (at 25°C)	%						±	0.5						±1
Hysteresis, 0.5 x F _{nom}	%								< 0.0	5				
Linearity error	%				<±0.05									
Effect of temperature on output span / 10K	%								< 0.5	,				
Drift, at 20 °C	pC/s					< 0.1							< 1	< 5
TEDS, as per IEEE1451.4									1-wire	е				
Measurement frequency range (-3 dB)	kHz					0 (–3 c 5 (–1 c	,						7 (-3 dB) 3.5 (-1 dB)	10 (-3 dB) 5 (-1 dB)
Supply voltage	V							24	(18	. 30)				
overvoltage and one-way fitting														
Voltage supply buffer capacitor	μF								22					
Galvanic isolation		Galvai	nic iso	lation	of sign	al inpu		charge t need				su	pply, the CMA	A housing does
Power consumption	W								< 1.2	2				
Output resistance	Ω								< 10					
Permissible load resistance	kΩ								> 5					
Control inputs														
Reset/Measure step	рC								< ±2	2				
Switching time for Reset/Measure	μs								< 100)				
Total time for Reset process	ms								75					
Measurement mode MEASURE	V						0) +5			put			
RESET	V							1	2 3	30				
Measurement range RANGE 1	V						0) +5	or or	en ir	tua			
RANGE 2	V						Ū		2 3					
Device signals					10–1	2UNF	So				torane	< ≤ ′	1.5 Nm	
Sensor						1, 8-pi	n, fo	or sign	al out	put, s	supply,	, dig	gital input	
Electrical connection						(sl	nielo	ded ca	ble re	com	mende	ed)		
Vibration resistance 20 2000 Hz, duration 16 min, cycle 2 min.	m/s ²								100					
Impact (duration 1 ms)	m/s ²								2000)				
Nominal temperature range	°C							(0 7	0				
Dimensions (L x W x H)	mm					5	7 x 4	46 x 3	8					72 x 46 x 39
Weight	g						1	130						
Housing material								A	lumin	um				
Degree of protection														
(with connected cables)									IP65					
EMC conformity as per EN 61326–1:2013, EN 61326–2–3:2016						i	n ar	n indus	strial e	enviro	nmen	t		

Customized measuring ranges are available on request.

Pin and cable assignment







Scope of supply

Order no.	
1-CMA1	Single-channel charge amplifier for piezoelectric sensors, measuring range 1 000 pC
1-CMA2	Single-channel charge amplifier for piezoelectric sensors, measuring range 2 000 pC
1-CMA5	Single-channel charge amplifier for piezoelectric sensors, measuring range 5 000 pC
1-CMA20	Single-channel charge amplifier for piezoelectric sensors, measuring range 20 000 pC
1-CMA39	Single-channel charge amplifier for piezoelectric sensors, measuring range 39 500 pC
1-CMA158	Single-channel charge amplifier for piezoelectric sensors, measuring range 158 000 pC
1-CMA210	Single-channel charge amplifier for piezoelectric sensors, measuring range 210 000 pC
1-CMA287	Single-channel charge amplifier for piezoelectric sensors, measuring range 287 000 pC
1-CMA482	Single-channel charge amplifier for piezoelectric sensors, measuring range 482 000 pC
1-CMA2000	Single-channel charge amplifier for piezoelectric sensors, measuring range 2 000 000 pC
1-CMA5000/2	Single-channel charge amplifier for up to 2 piezoelectric sensors, measuring range 5 000 000 pC

Accessories (not included in the scope of supply)

1-KAB168-5	8-wire cable to the voltage supply and processing electronics, M12 x 1 cable plug, 5 m long, free ends
1-KAB168-20	8-wire cable to the voltage supply and processing electronics, M12 x 1 cable plug, 20 m long, free ends
1-KAB143-3	Sensor connection cable, coaxial, socket 10–32 UNF at both ends, available in 2 m, 3 m and 7 m lengths
1-KAB145-3	Sensor connection cable, coaxial, socket 10–32 UNF at both ends, available in 0.2 m and 3 m lengths, robust design
1-CSB4/1	Summing box CSB4/1 with protective caps

Subject to modifications.

All product descriptions are for general information only. They are not to be understood as a guarantee of quality or durability.

Hottinger Baldwin Messtechnik GmbH

Im Tiefen See 45 · 64293 Darmstadt · Germany Tel. +49 6151 803-0 · Fax +49 6151 803-9100 Email: info@hbm.com · www.hbm.com

