

DATA SHEET


AED9101D Basis device for AD103C

SPECIAL FEATURES

- For static and dynamic applications
- RS-232, RS-422 or RS-485 interfaces
- Test report available for 10,000 digits, class III
- Trigger input
- 10 ... 30 V supply voltage range
- Degree of protection IP65
- · EMC protection
- · Diagnostic bus for analysis and additional display



DIMENSIONS



Dimensions (in mm; 1 mm = 0.03937 inches)

Туре			AED9101D
Measuring amplifier			AD103C
Measurement signal input		mV/V	± 3 , nominal ± 2
Transducer connection			
SG transducer (full bridge)		Ω	40 4000
Transducer connection type			6-wire circuit
Length of transducer cable		m	≤100
Bridge excitation voltage		V _{DC}	5
Interfaces			
Hardware (selected by slide-switch)			RS-232, RS-422, RS-485
Length of communications cable	RS-232	m	≤15
	RS-422, RS-485	m	≤1000
Max. number of bus nodes (RS-485)			32
Diagnosis bus (RS-485 2-wire)			
Protocol			ASCII/binary
Baud rate, max.		kbit/s	38.4
Node address			0 89
Length of communications cable, max.		m	1000
Trigger input			
Input voltage range, LOW		V	0 1
Input voltage range, HIGH		V	2 30
Input voltage range at High level = 30 V		mA	<3
Power supply			
Supply voltage		V_{DC}	10 30
Current consumption (without load cell)		mA	≤100 ¹⁾
Temperature range			
Nominal (rated) temperature		°C	-10 +40
Operating temperature			-20 +60
Storage temperature			-25 +85
Dimensions		mm	190 x 65 x 40
Weight, approx.		g	440 (without AD10x)
Degree of protection per EN 60529 (IEC 529)			IP65

¹⁾ Currentconsumption \leq 100mA + $\frac{ExcitationvoltageU_B = 5V}{BridgeresistanceR_B}$

Product numbers

1-AED9101D = Basic device AED9101D

1-AD103C = Amplifier board AD103C (see separate data sheet)

The complete documentation as well as parameterization and visualization software PanelX are available as a free download on the AED website: https://www.hbm.com/en/2561/aed-digital-transducer-electronics/

Im Tiefen See $45 \cdot 64293$ Darmstadt \cdot Germany Tel. +49 6151 803-0 \cdot Fax +49 6151 803-9100 www.hbkworld.com \cdot info@hbkworld.com