

#### **DATA SHEET**

# FS22DI Industrial BraggMETER DI

#### **SPECIAL FEATURES**

- Up to 8 connectors with parallel acquisition
- Dynamic selectable acquisition rates up to 1000 S/s
- NTP synchronization
- Catman® compatibility



### **DESCRIPTION**

FS22DI Industrial BraggMETER Interrogators are specifically designed to interrogate Fiber Bragg Grating (FBG) sensors. Based on continuous swept laser scanning technology, these Interrogators include a traceable wavelength reference that provides continuous calibration and ensures system accuracy over long term operation. The combination of high dynamic range and high output power allow high resolution to

be attained even for long fiber leads and/or lossy connections.

HBK FiberSensing Industrial BraggMETER interrogators run on a real-time operating system for consistent and deterministic acquisition of a large number of sensors provided by the combination of a broadband tuning range and the simultaneous and parallel acquisition over 1, 4 or 8 optical connectors.

## **BENEFITS AND APPLICATIONS**

#### Sensor design

- Laboratory and field deployment in Civil, Aeronautics, Energy and R&D applications
- Full control through SCPI Commands for integration in user's own software
- Multiple device or hybrid (electrical+optical) measurements possible by combining and synchronizing multiple interrogators and other HBK data acquisition devices


#### Fiber Bragg grating technology


- Absolute reference measurement
- Insensitive to EM/RF interferences
- Passive (can be used in Ex-areas)
- Intrinsic multiplexing capability reducing cabling requirements
- Long distances between sensors and the interrogators possible
- Combination of different sensor measurands

# **TECHNICAL DRAWING**

## Standard


Represented configuration with 8 FC/APC connectors






# **Rack Mountable**

Represented configuration with 8 FC/APC connectors





# **SPECIFICATIONS**

General						
Measurement range	nm	100 [1500 1600]				
Resolution/Repeatability <sup>1)</sup>	pm	<1.5				
Stability/Reproducibility <sup>1)</sup>	pm	5				
Optical connectors (simultaneous acquisition)	n.a.	1, 4 or 8				
Connector type	n.a.	FC/APC or SC/APC				
Sample rate <sup>2)</sup>	S/s	1000	500	200	100	50
Maximum number of detected FBG peaks						
Per OC	n.a.	31	63	127	127	127
Total		80 3)	96	200	400	600
Optical detection method	n.a.	Linear (selectable gain steps)				
Dynamic range <sup>4)</sup>	dB	> 25				
OSA <sup>5)</sup>	n.a.	Yes				
Optical output power per connector						
One connector	dBm	2				
Typical						
Maximum		3				
Four connectors						
Typical		-1				
Maximum		0				
Eight connectors						
Typical		-4				
Maximum		-3				
Power supply						
Standard	VDC	11 36				
Rack-mountable		100 240 (50 60Hz)				
Power connector						
Standard	n.a.	n.a. ODU Medi-Snap S11M08-P04MJGO-5280 <sup>7)</sup> C14 (IEC/EN 60320-1) <sup>8)</sup>				
Rack-mountable						
Consumption <sup>6)</sup>						
Peak	W	20				
Nominal	VV	8				
Stand by		2				

Communication					
Technology		Ethernet			
Connector	n.a.	RJ45			
Protocol		TCP/IP			
Syntax		SCPI <sup>9)</sup> (ASCII textual strings)			
Synchronization	n.a.	NTP			
Environmental and mechanical					
Operation temperature	°C	0 50			
Storage temperature	°C	-20 70			
Operation humidity	%	< 90% (at 40 °C)			
Storage humidity	%	< 95% (non-condensing)			
Mechanical tests <sup>10)</sup>					
Sinusoidal vibration (EN60068-2-6)					
Acceleration	g0-pk	2.5			
Duration per axis	min	30			
Frequency	Hz	5 65			
Random vibration (EN60068-2-64)					
Acceleration	g0-pk	9			
Power Spectral Density	min	1			
Frequency	Hz	10 500			
Shock resistance (EN60068-2-27)					
Acceleration	g0-pk	20			
Pulse duration	ms	11			
Dimensions (w x h x d)					
Standard	mm	155 x 125 x 275			
Rack-mountable		483 x 88 x 400			
Weight					
Standard	kg	4.5			
Rack-mountable		7			
Enclosure Material	n.a.	Aluminum			
Degree of protection (EN60529; IEC529)					
Standard	n.a.	IP40			
Rack-mountable		IP20			
EMC requirements	n.a.	Per EN 61326			

Measurements carried out using calibrated instrument against a NIST traceable gas cell. Accuracy as per NIST Technical Note 1297. Further details on HBK FiberSensing technical notes.

2) All available, user selectable.

5) Optical Spectral Analysis (1S/s refresh rate; 7050 points per sample, ~15 pm resolution)

6) Typical values. Peak consumption may reach 50 W (during start up).

8) Supplied with international AC plug cables.

9) Standard Commands for Programmable Instruments.

<sup>3)</sup> For 1000 S/s acquisition rate the presented values are valid when operating the device with catman® or SCPI commands with binary format reply. For operation with BraggMONITOR DI or SCPI commands with ASCII format reply, the maximum number of sensors, in total is 48.

Onsidered as the ratio between the optical power emitted at an optical connector and the minimum detectable optical power reflected by a fiber Bragg grating.

<sup>7)</sup> Supplied with 100 ... 240 V power adapter with international AC plugs and 1.5 m cable length. For additional orders use 1-NTX001 material number.

<sup>10)</sup> During tests the interrogator is powered off. The correct functioning of the equipment is confirmed after the test (transport simulation).

13 - 19" rack (RM) - SC/APC

500 - Dynamic (up to 1000S/s)

Configurable Item K-FS22 - 1 - 2 - 3

**Options** 

2

3

01 - Standard (ST) - FC/APC; 03 - Standard (ST) - SC/APC; 11 - 19" rack (RM) - FC/APC;

120 - 1 optical connector; 420 - 4 optical connectors; 820 - 8 optical connectors

<sup>11)</sup> Standard Items correspond to a configuration: Standard format and FC/APC connectors. With 4 or 8 optical connectors.