

OIML Certificate

OIML Member Stat The Netherlands	e	Number R60/2000-A-NL1-18.11 Project number 1902026 Page 1 of 2
 Issuing authority 	NMi Certin B.V. Person responsible: C. Oosterman	
Applicant and	Hottinger Baldwin Messttechnik GmbH	
Manufacturer	Im Tiefen See 45 D-64293 Darmstadt	
	Germany + + + + + + + + + + + + + + + + + + +	
Identification of the certified type	A single point load cell , with strain gaug Type : P ¹	ges. W37P
* * * * * * * *	* * * * * * * * * * * * * * * *	* * * * * * * * * * * * * *
+ Characteristics + +	See next page	
This OIML Certificate	e is issued under scheme A.	
+ identified in the OIM	ts the conformity of the above identified Type IL Test Report) with the requirements of the for zation of Legal Metrology (OIML): OIML R 60 - Edition 2000 (E) for accuracy of	ollowing Recommendation of the + + +
instrument covered k	es only to the metrological and technical chara by the relevant OIML International Recommend not bestow any form of legal international ap	dation above-identified. + + + + + +
OIML Member State	rt from the mention of the Certificate's referent in which the Certificate was issued, partial quo Test Report(s) is not permitted, although eithe	otation of the Certificate and of
+ + + + + + + +	* * * * * * * * * * * * * * *	* * * * * * * * * * * * * *
Issuing Authority	NMi Certin B.V., OIML Issuing Authorit 15 May 2018	Y NL1 + + + + + + + + + + +
	C. Oosterman Head Certification Board	
NMi Certin B.V. Hugo de Grootplein 1 3314 EG Dordrecht the Netherlands T +31 78 6332332 certin@nmi.nl www.nmi.nl	This document is issued under the provision that no liability is accepted and that the applicant shall indemnify third-party liability. The notification of NMi Certin B.V. as Issuing Authority can be verified at www.oiml.org	INSPECTION RVA 122





OIML Member State The Netherlands Number R60/2000-A-NL1-18.11 Project number 1902026 Page 2 of 2

* * * * * * * * * * * * * * * * *	* * * * * * * * * * * * * * * * * *	
Maximum capacity (E _{max})	50 kg up to and including 200 kg	
Minimum dead load	• • • • • • • 0 kg	
Accuracy Class	· · · · · · · · · · · · · · · · · · ·	
Rated Output	2 mV/V	
Maximum number of load cell intervals (n) ⁽¹⁾	6000	
Ratio of minimum LC Verification interval ⁽¹⁾ Y = E_{max} / v_{min}	25000	
Ratio of minimum dead load output return ⁽¹⁾ Z = E_{max} / (2 * DR)	+ + + + + + + 6000 + + + + + + + + + + +	
Input impedance	380 Ω ± 15 Ω	
Temperature range	-10 °C / + 40 °C	
Fraction p_{LC} + + + + + + + + + + + + +	+ + + + + + 0,7 + + + + + +	
Humidity Class	сн • • • • • • сн • • • • • •	
Safe overload	150 % of E _{max}	
Output impedance	360 Ω ± 10 Ω	
Recommended excitation	5 V AC / DC	
Excitation maximum	15 V AC / DC	
Transducer material	Stainless steel	
Atmospheric protection + + + + + + + + +	+ + + Hermetically welded	
 The characteristics for n_{max}, Y and Z can be re 1. The characteristics for n_{max}, Y and Z can be re Fach load cell produced is provided with an accompandaracteristics. The above identified Type (represented by the samplound to comply with the additional national require United States of America (NIST Handbook 44 and NC Declaration: R 60 OIML-CS rev.2Additional requirements from R 60 OIML-CS rev.2 Additional requirements from 	nying document with information about its e(s) identified in the OIML Test Report) have bee ements established by the WM Publication 14), included in the Utilizer the United StatesAccuracy class III L;	