


# Load cells

HLCF1C3 550kg

#### **Special features**

- Hermetically encapsulated (IP68)
- Maximum capacities: 220 kg ... 1.76 t
- Rust-resistant materials
- Low height of construction
- Meets EMC requirements as per EN 45501:2015
- Legal for trade as per OIML R60 to 3000 divisions

Cable assignment (6-wire configuration)






## Specifications

Type HLC F2     Maximum capacity (E <sub>max</sub> )     (Load application = blind hole + integrated overload stored)	HLC F2 C3 / 220 kg; 550 kg; 1.1 t; 1.76 t						
Accuracy class per OIML R60	C3						
Number of load cell verification intervals	n <sub>LC</sub>		3000				
Minimum load cell verification interval	V <sub>min</sub>	% of maximum capacity (E <sub>max)</sub>	0.0100 (220 kg; 1.76 t) 0.0090 (550 kg; 1.1 t)				
Ratio of minimum verification interval Y	Y		10,000 (220 kg; 1.76 t) 11,111 (550 kg; 1.1 t)				
General specifications							
Rated output (nominal)	C <sub>N</sub>	mV/V	1.94				
Rated output tolerance		%	±0.1				
Temperature coefficient of zero signal	TC <sub>0</sub>	% of C <sub>n</sub> /10 K	±0.0140 (220 kg; 1.76 t;) ±0.0126 (550 kg; 1.1 t)				
Temperature coefficient of sensitivity <sup>1)</sup>	TCS		±0.0140				
Relative reversibility error <sup>1)</sup>	d <sub>hy</sub>		±0.0166				
Non-linearity <sup>1)</sup>	d <sub>lin</sub>	% of C	±0.0170				
Creep upon loading in 30 min.	d <sub>cr</sub>	% of C <sub>n</sub>	±0.0166				
Minimum dead load output return	MDLOR		±0.0166				
Input resistance	$R_{LC}$	Ω	350 480				
Output resistance	R <sub>0</sub>	Ω	350 ±2				
Reference voltage	U <sub>ref</sub>	V	5				
Nominal (rated) range of the supply voltage	Β <sub>U</sub>	V	0.5 15				
Insulation resistance	R <sub>is</sub>	GΩ	> 5				
Nominal (rated) range of the ambient temperature	B <sub>T</sub>		-10 +40				
Operating temperature range	B <sub>tu</sub>	°C	-30 +70				
Storage temperature range	B <sub>tl</sub>		-50 +85				
Limit load	EL		150				
Lateral loading limit	Elq	% of	100				
Breaking load	Ed	maximum capacity	300				
Relative permissible vibrational stress (oscillation width as per DIN 50100)	F <sub>srel</sub>	(E <sub>max)</sub>	70				
Rated displacement at E <sub>max</sub> , approx.	s <sub>nom</sub>	mm	0.5 (1.76 t = 1.4 mm)				
Weight, approx.	m	kg	0.9 (220 kg 1.76 t)				
Degree of protection per EN 60 529 (IEC 529)			IP68				
<b>Material</b> Measuring body Cable entry Cable sheath			Stainless steel <sup>2)</sup> Stainless steel/seal: Viton <sup>®</sup> PVC				

<sup>1)</sup> The values for non-linearity (d<sub>lin</sub>), relative reversibility error (d<sub>hy</sub>) and temperature coefficient of sensitivity (TC<sub>S</sub>) are recommended values. The sum of these values is within the accumulated error limit specified by OIML R60.
<sup>2)</sup> As per EN 10088-1

### Dimensions (in mm)





Maximum capacity	Α	В	С	D	Е	F	G	Н	J	К	ØL	М	Ν
220 kg; 550 kg; 1.1 t	133.4	30.2	30.7	57.7	15.4	76.2	25.4	1.7	13	3 m	20.6	M12	14.2
1.76 t	133.4	30.2	30.7	51.7	15.4	76.2	25.4	1.7	13	3 m	20.6	M12	14.2

#### Mounting accessories (to be ordered separately)

To minimize error effects from load application, HBM offers different tried and tested load application elements for type HLC **F2** ... load cells based on the mounting conditions.

### Accessories for HLC F ... (to be ordered separately; dimensions in mm)





Subject to modifications.

All product descriptions are for general information only. They are not to be understood as a guarantee of quality or durability. Hottinger Brüel & Kjaer GmbH Im Tiefen See 45 · 64293 Darmstadt · Germany Tel. +49 6151 803-0 · Fax +49 6151 803-9100 Email: info@hbm.com · www.hbm.com



# measure and predict with confidence