

Issued by NMI Certin B.V.

In accordance with WELMEC 8.8 2017, WELMEC 2.4 Issue 2, OIML R 60 (2017), EN 45501:2015.

Producer Hottinger Baldwin Messtechnik GmbH
Im Tiefen See 45
D-64293 Darmstadt
Germany

Measuring instrument A **single point load cell**, with strain gauges, tested as a part of a weighing instrument.

Registered trade name : HBM
Designation : PW16A...

Further properties are described in the annexes:

- Description TC11923 revision 0;
- Documentation folder TC11923-1.

An overview of performed tests is given in the annex:

- Description TC11923 revision 0.

Issuing Authority

NMI Certin B.V.
30 June 2020

Certification Board

NMI Certin B.V.
Thijssseweg 11
2629 JA Delft
The Netherlands
T +31 88 6362332
certin@nmi.nl
www.nmi.nl

This document is issued under the provision that no liability is accepted and that the producer shall indemnify third-party liability.

Reproduction of the complete document only is permitted.

This document is digitally signed and sealed. The digital signature can be verified in the blue ribbon at the top of the electronic version of this certificate.

1 General information about the load cell

All properties of the load cell, whether mentioned or not, shall not be in conflict with the standards mentioned in this certificate.

This certificate is the positive result of the applied voluntary, modular approach, for a component of a measuring instrument, as described in WELMEC 8.8. The complete measuring system must be covered by an EC type-approval certificate, an EC-type examination certificate or an EU-type examination certificate.

1.1 Essential parts

Number	Pages	Description	Remark
11923/0-01	1	PW16A... outline drawing	Mechanical
11923/0-02	1	Wiring diagram	Electrical

Cable:

- The load cell is provided with a 6-wire system (=“Remote-sensing”):
 - The cable length is not limited.

The cable is shielded; the shield is connected to the load cell.

1.2 Essential characteristics

Characterization of load cell capabilities	Analog-Passive load cell
Maximum capacity (E_{max})	30 kg up to and including 660 kg
Minimum dead load	0 kg
Accuracy Class	C
Rated Output	2 mV/V \pm 0,2 mV/V
Maximum number of load cell intervals (n) ⁽¹⁾	4000
Ratio of minimum LC Verification interval ⁽¹⁾ $Y = E_{max} / V_{min}$	20000
Ratio of minimum dead load output return ⁽¹⁾ $Z = E_{max} / (2 * DR)$	5000
Input impedance	400 Ω \pm 100 Ω
Temperature range	-10 °C / +40°C
Fraction p_{LC}	0,7
Humidity Class	CH
Safe overload	150 % of E_{max}
Output impedance	400 Ω \pm 100 Ω

Recommended excitation	5 V AC / DC
Excitation maximum	15 V AC / DC
Transducer material	Aluminium
Atmospheric protection	Silicone rubber

Remark:

1. The characteristics for n_{max} , Y and Z can be reduced separately.

1.3 Essential shapes

Number	Pages	Description	Remark
11923/0-01	1	PW16A... outline drawing	Mechanical

The descriptive markings plate is secured against removal by sealing or will be destroyed when removed and contains at least the information and markings as described in OIML R 60 (2017) and:

- This certificate number TC11923 (in the countries where it is mandatory);
- Producers name or mark.

2 Seals

The connecting cable of the load cell or the junction box is provided with possibility to seal.

3 Conditions for conformity assessment

The compatibility of load cells and indicator is established by the manufacturer by means of the compatibility of modules form, contained in EN45501:2015 clause F.4 at the time of putting into use.

Other parties may use this certificate without the written permission of the producer.

4 Reports

An overview of performed tests is given in the reports:

- No. NMI-2433151-01 dated 30 June 2020 that includes 51 pages;
- No. NMI-2433151-02 dated 30 June 2020 that includes 46 pages.

A report can be a test report, an evaluation report, a type evaluation report and/or a pattern evaluation report.