
FIT®/5...

Digital load cell for dynamical weighing




Special features

- 4 limit switches with hysteresis
- Dosing functionalities and diagnostic channel (Type E)
- integrated overload protection (Patent announced)
- Trigger function (external or level trigger)
- PC-Software for parameter adjustment and dynamical analysis
- hermetically sealed stainless steel housing IP68
- Test report for 3000 d accord. to OIML R 60, R 76










The FIT/... digital load cells are available in different versions, e.g.:



HBM has defined so-called preferred variants. All other variants are available on request.

Preferred variants of the standard types

Housing	Housing Interface			
	RS-232	RS-485 (4 wire)	CANOpen	DeviceNet
FIT/0	1-FIT/0SA30/5KG 1-FIT/0SA30/10KG 1-FIT/0SA30/20KG 1-FIT/0SA30/50KG 1-FIT/0SA30/75KG	1-FIT/0SB30/5KG 1-FIT/0SB30/10KG 1-FIT/0SB30/20KG 1-FIT/0SB30/50KG 1-FIT/0SB30/75KG	1-FIT/0SC30/5KG 1-FIT/0SC30/10KG	1-FIT/0SD30/5KG 1-FIT/0SD30/10KG
FIT/1	1-FIT/1SA31/5KG 1-FIT/1SA31/10KG 1-FIT/1SA31/20KG 1-FIT/1SA31/50KG 1-FIT/1SA31/75KG	1-FIT/1SB31/5KG 1-FIT/1SB31/10KG 1-FIT/1SB31/20KG 1-FIT/1SB31/50KG 1-FIT/1SB31/75KG 1-FIT/1SB32/5KG 1-FIT/1SB32/10KG 1-FIT/1SB32/20KG	1-FIT/1SC31/5KG 1-FIT/1SC31/10KG	1-FIT/1SD31/5KG 1-FIT/1SD31/10KG
FIT/4		1-FIT/4SB32/5KG 1-FIT/4SB32/10KG 1-FIT/4SB32/20KG		
FIT/5	1-FIT/5SA30/5KG 1-FIT/5SA30/10KG 1-FIT/1SA30/20KG		1-FIT/5SC30/5KG 1-FIT/5SC30/10KG	

Preferred variants of the extended types

In addition to the standard version (S), another extended version (E) with control functions (two connectors) is available. All versions offers additional application areas with limit values and dosing control functions (e.g. sorting systems, filling systems).

Housing	Housing Inteface			
	RS-232	RS-485 (4 wire)	CANOpen	DeviceNet
FIT/0	1-FIT/0EA30/5KG 1-FIT/0EA30/10KG 1-FIT/0EA30/20KG 1-FIT/0EA30/50KG 1-FIT/0EA30/75KG	1-FIT/0EB30/5KG 1-FIT/0EB30/10KG 1-FIT/0EB30/20KG 1-FIT/0EB30/50KG 1-FIT/0EB30/75KG	1-FIT/0EC30/5KG 1-FIT/0EC30/10KG	1-FIT/0ED30/5KG 1-FIT/0ED30/10KG
FIT/1	1-FIT/1EA31/5KG 1-FIT/1EA31/10KG 1-FIT/1EA31/20KG 1-FIT/1EA31/50KG 1-FIT/1EA31/75KG	1-FIT/1EB31/5KG 1-FIT/1EB31/10KG 1-FIT/1EB31/20KG 1-FIT/1EB31/50KG 1-FIT/1EB31/75KG	1-FIT/1EC31/5KG 1-FIT/1EC31/10KG	1-FIT/1ED31/5KG 1-FIT/1ED31/10KG
FIT/4	-	1-FIT/4EB31/5KG 1-FIT/4EB31/10KG 1-FIT/4EB32/5KG 1-FIT/4EB32/10KG	1-FIT/4EC31/5KG 1-FIT/4EC31/10KG	1-FIT/4ED31/5KG 1-FIT/4ED31/10KG
FIT/5	1-FIT/5EA30/5KG 1-FIT/5EA30/10KG	1-FIT/5EB30/5KG 1-FIT/5EB30/10KG	1-FIT/5EC30/5KG 1-FIT/5EC30/10KG 1-FIT/5EC30/20KG	1-FIT/5ED30/5KG 1-FIT/5ED30/10KG

⁼ for these load cell types separate data sheets are available

Specifications

Туре			FIT/5	
Accuracy class according to OIML R60			C3	
Max. capacity (E _{max})	ka	5	10	20
Min. load cell verification interval (v _{min})	kg	0.5	10	20
Min. application range for 3000 d	g	1.5	3	6
•	kg	1.3		0
Max. platform size	mm		L 400 x W 400	
Max. number of load cell verification intervals (n _{LC})			3000	
Apportionment factor (p _{LC})			1	
Temperature effect on sensitivity (TK _C) ^{1) 2)}	0/ of			
in temperature range 0 °C+40 °C [+32 °F+104 °F]	% of C _n /10K		± 0.0250	
Temperature effect on zero signal (TK _{S0}) ²⁾	C _n / TOR		± 0.0200	
Hysteresis factor (d _{hv}) ^{1) 2)}			±0.0166	
Nonlinearity (d _{lin}) ^{1) 2)}			± 0.0166	
· · · · · · · · · · · · · · · · · · ·	% of C _n			
Creep (d _{CR}) over 30 min			± 0.0166	
Eccentric loading error acc. to OIML R76			±0.0233	
Service load (E _U); max. 120 mm eccentricity			150	
Safe load limit (E _L); max. 20 mm eccentricity	% of		1000	
Permissible dyn. load (F _{srel})	E _{max}		_	
max. 50 mm eccentricity			70	
Deflection at max. capacity (s _{nom})	mm	·	< 0.15	
Power supply:				
Supply voltage UB1 (DC)	V		+ 10 +30	
Power consumption	W		< 2	
Switch-on current	A		≦ 2	
			0.2	
Resolution of meas. signal (1 Hz-Filter)	Bit		20	
Measuring rate	1/s		4 1200	
Adjustable cut-off frequency of the digital filters				
Filtermode 0	Hz		200 0.25	
Filtermode 1 (response time 62 365 ms)	Hz		18 2.5	
Baud rate (RS-232-, RS-485-interface)	Baud	1200; 2400;	; 4800; 9600; 19	200; 38400;
			57600; 115200	
Max. number of bus members			90	
CANopen interface		St	andard CiA DS3	01
Baud rate	Baud		0 000 1 000 00	
DeviceNet interface		R	elease 2.0 ODV	A
Baud rate	Baud		25 000 500 00	
max. cable length (CANOpen, DeviceNet)	m			
max. Cable length (CANOpen, Devicence)	""	≥ 500	0 (10KBaud) ≤ (500KBaud),	100
			≤ 25 (1MBaud)
Diagnostic channel, RS-485-2-wire (extended version E, female dev. conn. 2)			_ 20 (1111Bada	,
Baud rate	Poud		38 400	
	Baud			
max. cable length	m		500	
Max. number of bus members			90	
Asynchronous serial interface (female device connector 1)				
RS-485, 4 wire, max. cable length	m		500	
RS-232 max. cable length	m		15	
Trigger input (female device connector 1)				
Permissible input voltage	1		0 +12	
Low-level	V		. 4	
High Javel	V		< 1	
High-level			< 1 > 4	
High-level Input resistance	V			
Input resistance	V	isolated	> 4 10	ial GND2
Input resistance Control inputs (extended version E, female device connector 2)	V V kΩ	isolated,	> 4 10 reference potent	ial GND2
Input resistance Control inputs (extended version E, female device connector 2) Permissible input voltage	V V kΩ	isolated,	> 4 10 reference potent 0 +30	ial GND2
Input resistance Control inputs (extended version E, female device connector 2) Permissible input voltage Low-level	V V kΩ V	isolated,	> 4 10 reference potent 0 +30 < 6	ial GND2
Input resistance Control inputs (extended version E, female device connector 2) Permissible input voltage Low-level High-level	V V kΩ V V	isolated,	> 4 10 reference potent 0 +30 < 6 > 10	ial GND2
Input resistance Control inputs (extended version E, female device connector 2) Permissible input voltage Low-level High-level Input resistance	V V kΩ V		> 4 10 reference potent 0 +30 < 6 > 10 > 3	
Input resistance Control inputs (extended version E, female device connector 2) Permissible input voltage Low-level High-level Input resistance Control outputs (extended version E, female device connector 2)	V V kΩ V V kΩ		> 4 10 reference potent 0 +30 < 6 > 10 > 3 reference potent	
Input resistance Control inputs (extended version E, female device connector 2) Permissible input voltage Low-level High-level Input resistance Control outputs (extended version E, female device connector 2) External supply voltage UB2	V V kΩ V V		> 4 10 reference potent 0 +30 < 6 > 10 > 3 reference potent +11 +30	
Input resistance Control inputs (extended version E, female device connector 2) Permissible input voltage Low-level High-level Input resistance Control outputs (extended version E, female device connector 2) External supply voltage UB2 Max. current of one output	V V kΩ V V kΩ		> 4 10 reference potent 0 +30 < 6 > 10 > 3 reference potent	
Input resistance Control inputs (extended version E, female device connector 2) Permissible input voltage Low-level High-level Input resistance Control outputs (extended version E, female device connector 2) External supply voltage UB2	V V kΩ V V kΩ		> 4 10 reference potent 0 +30 < 6 > 10 > 3 reference potent +11 +30	


¹⁾ The values can be exceeded in individual cases. The resulting errors of TK_C , nonlinearity and hysteresis don't exceed the maximum permissible errors of OIML R 60 with $p_{LC} = 1$.

²⁾ All relative errors are related to the output signal at max. capacity.

Specifications (continuation)

Nominal temperature range	°C [°F]	-10 +40 [+14 +104]
Operating temperature range	°C [°F]	-10 +50 [+14 +122]
Storage temperature range	°C [°F]	–25 +75 [–13 +167]
EMC-requirements		EN 45501, OIML R76
		EN 61326-1/Tab. 4, equipment of class B
		EN 61326/A1, Tab. A1, equipment in industrial
		areas
Degree of protection acc. to EN 60529		IP 68
Female device connector		Female device connector, Fa. Lumberg, 8-pole
Material		Stainless steel
Weight, approx.	kg	2

Electrical connection



Female device connector 1				Female device conn. 2 (optional)		
Pin-No.	RS-232	RS-485	CANOpen/DeviceNet	Pin-No.		
7	TxD	TA	CANH out	1	OUT 1	
3	RxD	RA	CANH in	2	OUT 2	
6	_	TB	CANL out	3	OUT 3	
5	=	RB	CANL in	4	OUT 4	
8	UB 1	UB 1	UB 1	5	UB 2	
1	GND 1	GND 1	GND 1	6	GND 2	
4 1)	Diag. Ra/Ta or Trigger	Diag. Ra/Ta or Trigger	Diag. Ra/Ta or Trigger	7	IN 1	
2 1)	Diag. Rb/Tb	Diag. Rb/Tb	Diag. Rb/Tb	8	IN 2	

¹⁾ The standard version (S) does not have a diagnostic channel. Pin 2 is not assigned, Pin 4 is trigger input.

Accessories, to be ordered separately

Connection cable

Material: PUR, \emptyset 7 \pm 0.5 mm, Female device connector / free ends

Length	3 m
Cable (8 cores)	1-KAB165-3*)

^{*)} The cable is suitable only for experimental purposes for the structure of CANOpen and DeviceNet bus systems (the characteristic wave impedance does not correspond to the CANOpen specifications)

- **1-FIT-AED-DOC** = Documentation (CD-ROM with Operating manual and AED-Panel program AED_Panel32)
 - Documentation of mechanics and electronics
 - Documentation of command codes for the communication with the FIT/5... load cell
 - Software package for parameter setting and dynamic analysis of the weighing system
- **1-FIT-AED-KIT** = Starter kit for CANOpen and DeviceNet

Modifications reserved.

All details describe our products in general form only. They are not to be understood as express warranty and do not constitute any liability whatsoever.

Hottinger Baldwin Messtechnik GmbH

Im Tiefen See 45, D-64293 Darmstadt, Germany Tel.: +49 6151 803-0 Fax: +49 6151 803 9100 Email: support@hbm.com Internet: www.hbm.com

